

Closed chamber weld heads MW 40/65/115/170

Orbital welding heads for tube-to-tube welding

Standard equipment

Closed chamber weld head with hosepack 5,5 m Protection chamber for gas-covering to avoid coleration Compact design for use in areas with limited access "Solid Flex" titanium tube clamps for optimum hold and positioning

Special gas arrival to avoid particle emissions
Consistent high quality welding due to water cooling
DC-motor drive with encoder-system (quick change)
Transport case

Viewport for weld joint inspection

Modular clamping insert-system (quick change) Integrated control buttons with following functions:

- Rotation movement, gas & water-circuit test (out of weld cycle)
- Start cycle, downslope, stop (during weld cycle)

Recommended base materials:

- Stainless steel
- Titanium
- Inconel
- Aluminium (limited) etc.

Recommended areas of use:


Special for welding of thin-walled tubes and high productivity applications (tube outer diameter 6,0 up to 170 mm, wall thickness max. 3,5 mm)

- Microelectronics
- · Pharmacy/Biochemical industry
- Food industry
- · Climate industry
- · Aerospace/ Aeronautics
- Measurement sensors





Robledo e Hijos. · Moyano 1259, Adrogué 1846 Buenos Aires Telefax: 054-11-4293-5775 / 5838 / 4115-1077 info@ryhsa.com.ar www.ryhsa.com.ar



Process

TIG DC or TIG AC/DC welding (flush joint) of pipes without filler wire

Accessories

Clamping inserts (Titanium) for one tube outer-diameter Special designed clamping inserts Adaptor for clamping inserts of previous MW-models Offset electrode holder (tubes with reduced straight length) Shield for one tube outer-diameter (tube-elbow) Extension hosepack

Technical data	Tube outer diameter	Dimensions					
		Α	В	C	C*	D	E
MW 40	6 - 40 mm	100 mm	430 mm	38 mm	38 mm	19 mm	50 mm
MW 65	12 - 65 mm	126 mm	458 mm	38 mm	57,5 mm	19 mm	63 mm
MW 115	25 - 115 mm	200 mm	547 mm	46 mm	68 mm	23 mm	100 mm
MW 170	80 - 170 mm	290 mm	580 mm	63 mm	63 mm	31,5 mm	145 mm

C* ... width with adaptor and clamping inserts of previous MW model



FRONIUS INTERNATIONAL GMBH

Buxbaumstraße 2, P.O.Box 264, A 4602 Wels Tel: +43/7242/241-0, Fax: +43/7242/241-3940 E-Mail: sales@fronius.com



